

19" Assembly Kit M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CERTIFICATIONS



FEATURES

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

SPECIFICATIONS

Material:	Steel; ABS
Product Type:	Assembly Kit
Type:	Mounting Kit
Finish:	Zinc Plated

Table 1/1

Catalog Number	Package Quantity	Thread Size	Product Family	Works With	Quick Ship
----------------	------------------	-------------	----------------	------------	------------

21100-435	8	M6	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	No
21101-809	50	M6	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	No
21101-810	100	M6	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Novastar, Eurorack, Outdoor	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	No
21190-435	32	M6	RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, Comptec, Inpac, MultipacPRO, Varistar CP, Eurorack, Outdoor	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE