

Heavy Duty T-Grid Box Hanger



CERTIFICATIONS



FEATURES

Quickly mounts a box to T-grid

Adjustable height for various electrical box depths

Mounts flush with face of tile

Installs by hand

Drop wire for independent support from clip and/or bar

Screws easily to tee bar for added stability

Supports multiple box installations

SPECIFICATIONS

Table 1/1

Catalog Number	Material	Finish	Included Components	Length	Box Depth	Ultimate Static Load
512HD	Steel, Spring Steel	Pregalvanized, nVent CADDY Armour	Mounting Clip	609.6mm	38mm, 54mm	220N

ADDITIONAL PRODUCT DETAILS

Standard bar mounts 2 1/8" box. Break off tabs for 1 1/2" deep box. Mounts flush with face of tile.

512HDEEP Series with additional 512HDXT mounts 2 1/8" deep box with 1 1/2" extension ring.

Not permitted for paddle fans.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

