

# nVent CADDY Cat HP J-Hook with Pin Driven Angle Bracket



## CERTIFICATIONS



## FEATURES

Longer leg angle bracket for tool clearance

Designed to fit a variety of pin drivers

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

## SPECIFICATIONS

**Finish:** Pregalvanized

**Material:** Steel

Table 1/2

| Catalog Number   | Article Number | Diameter (Ø) | Area                | Cable Capacity, Cat 5e | Cable Capacity, Cat 6 | Cable Capacity, Cat 6A |
|------------------|----------------|--------------|---------------------|------------------------|-----------------------|------------------------|
| CAT16HPAFAB<br>3 | 181009         | 25 mm        | 690mm <sup>2</sup>  | 20                     | 15                    | 10                     |
| CAT21HPAFAB<br>3 | 181191         | 33.3 mm      | 1174mm <sup>2</sup> | 50                     | 40                    | 25                     |
| CAT32HPAFAB<br>3 | 181011         | 50 mm        | 2561mm <sup>2</sup> | 90                     | 60                    | 35                     |
| CAT48HPAFAB<br>3 | 181233         | 75 mm        | 5974mm <sup>2</sup> | 200                    | 150                   | 80                     |
| CAT64HPAFAB<br>3 | 181223         | 100 mm       | 9987mm <sup>2</sup> | 330                    | 220                   | 140                    |
| CAT21HPAFAB<br>4 | 181192         | 33.3 mm      | 1174mm <sup>2</sup> | 50                     | 40                    | 25                     |
| CAT32HPAFAB<br>4 | 181012         | 50 mm        | 2561mm <sup>2</sup> | 90                     | 60                    | 35                     |
| CAT48HPAFAB<br>4 | 181234         | 75 mm        | 5974mm <sup>2</sup> | 200                    | 150                   | 80                     |
| CAT64HPAFAB<br>4 | 181224         | 100 mm       | 9987mm <sup>2</sup> | 330                    | 220                   | 140                    |
| CAT21HPAFAB<br>6 | 181193         | 33.3 mm      | 1174mm <sup>2</sup> | 50                     | 40                    | 25                     |
| CAT32HPAFAB<br>6 | 181013         | 50 mm        | 2561mm <sup>2</sup> | 90                     | 60                    | 35                     |
| CAT48HPAFAB<br>6 | 181235         | 75 mm        | 5974mm <sup>2</sup> | 200                    | 150                   | 80                     |
| CAT64HPAFAB<br>6 | 181225         | 100 mm       | 9987mm <sup>2</sup> | 330                    | 220                   | 140                    |

Table 2/2


| Catalog Number | Article Number | Hole Size (HS) | Static Load |
|----------------|----------------|----------------|-------------|
| CAT16HPAFAB3   | 181009         | 4 mm           | 270N        |
| CAT21HPAFAB3   | 181191         | 4 mm           | 270N        |
| CAT32HPAFAB3   | 181011         | 4 mm           | 270N        |
| CAT48HPAFAB3   | 181233         | 4 mm           | 270N        |
| CAT64HPAFAB3   | 181223         | 4 mm           | 270N        |
| CAT21HPAFAB4   | 181192         | 6 mm           | 270N        |
| CAT32HPAFAB4   | 181012         | 6 mm           | 270N        |
| CAT48HPAFAB4   | 181234         | 6 mm           | 270N        |
| CAT64HPAFAB4   | 181224         | 6 mm           | 270N        |
| CAT21HPAFAB6   | 181193         | 9 mm           | 270N        |
| CAT32HPAFAB6   | 181013         | 9 mm           | 270N        |
| CAT48HPAFAB6   | 181235         | 9 mm           | 270N        |
| CAT64HPAFAB6   | 181225         | 9 mm           | 270N        |

## ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

