

Adjustable Steel Vented Shelf

Data Solutions



The Adjustable Steel Vented Shelf is adjustable from front to back in 25-mm increments. It is designed to support networking equipment within an open-frame rack. The shelf mounts to either the front or rear flange of an open-frame rack. The shelf's load rating is 60 lb. (27.2 kg)

FEATURES

The Adjustable Steel Vented Shelf is adjustable from front to back in 25-mm increments

It is designed to support networking equipment within an open-frame rack

The shelf mounts to either the front or rear flange of an open-frame rack

The shelf's load rating is 60 lb. (27.2 kg)

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
ESHVA19	21829	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
ESHVA23	21839	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm

Table 2/2

Catalog Number	Article Number	Rack Units	Width	Height	Depth
ESHVA19	21829	2U	10922mm	89mm	400mm
ESHVA23	21839	2U	12852mm	89mm	400mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE