

# Door Contact Switch Without Cable

## Data Solutions



Door contact switch with magnetic contact, allows operational efficiency. This product is easy handlable by plug and play.

## CERTIFICATIONS



## FEATURES

Door contact switch (without connection cable)

## SPECIFICATIONS

Table 1/2

| Catalog Number | Depth  | Height | Operating Temperature | Protection Rating | Width | Complies With            |
|----------------|--------|--------|-----------------------|-------------------|-------|--------------------------|
| 20118-810      | 33.5mm | 76.5mm | -25 to 75°C           | IP66              | 31mm  | UL® 508, EN 50047 form B |

Table 2/2

| Catalog Number | Current Rating | Package Quantity | Voltage   | Wire Size                |
|----------------|----------------|------------------|-----------|--------------------------|
| 20118-810      | 3 – 6A         | 1                | 24 – 230V | 0.5 – 2.5mm <sup>2</sup> |

## ADDITIONAL PRODUCT DETAILS

---

Please order bracket for installation of door switch (Varistar, Novastar, Eurorack) separately.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**