

ProLine S1 Server Package End, 2363x808x1198, Jet Black, Mild Steel

Data Solutions

CATALOG NUMBER

PS1SPE23812B



ProLine S1 Server Package Cabinets are an economical solution for contractors, small computer rooms, schools, retail outlets, or smaller networks that require a general purpose cabinet to house servers, switches, cables and other communication equipment. Multiple sizes, configurations, and accessories give ProLine S1 Cabinets wide application flexibility. ProLine S1 Server Packages are a data center-ready solution designed to be configured in a row or stand-alone configuration. The cabinets feature airflow management and provide easy cable access/mounting provisions.

INDUSTRY STANDARDS

UL 2416 Listed File Number E230874

cUL Listed per CSA 22.2 60950-1-07

UL 2416 Bonding and Grounding (with use of PGK grounding Kit)

EIA 310-D (RU – Rack Unit spacing, marking, and positioning)

IEC 60529, IP20

FEATURES

Top panel has four-corner brush strip cable entry

Internal airflow management

Cable management (750mm and 800mm wide models)

Plinth base

Ability to externally mount cable management (i.e. ladder rack)

Caster/leveler kit pre-installed

PDU mounting brackets included (qty 2 pair)

Joining kits included with “middle” configurations

PRODUCT ATTRIBUTES

Article Number: 59077
Height: 2363mm
Width: 808mm
Depth: 1198mm
Material: Mild Steel
Finish: Powder Coated
Color: Jet Black
Color Code: RAL 9005
Thickness: 1.52mm
Rack Units: 48U
Vertical Cable Manager Accessory: Yes
Side Covers Included: Yes
Type: End Section

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE