

Universal Transient Barrier, Single Pair Isolated Ground



CERTIFICATIONS



FEATURES

Compact design universal transient barrier provides protection of low-voltage circuits and transducers

Separate plug and base design allows hot swappable module replacement

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions

Surge rating to 20 kA 8/20 μ s is ideal for exposed wiring

Allows for protection of 25 analog signals or 50 digital signals per linear foot (0,3 m) of DIN rail space

SPECIFICATIONS

Catalog Number	UTB110SPG	UTB15SPG	UTB30SPG	UTB5SPG	UTB60SPG
Article Number	702878	702874	702876	702873	702877
Nominal System Voltage (Un)	100 - 120 VAC 60 - 154 VDC	3 - 10 VAC 5 - 15 VDC	10 - 21 VAC 15 - 30 VDC	0 - 3 VAC 0 - 5 VDC	21 - 42 VAC 30 - 60 VDC

Catalog Number	UTB110SPG	UTB15SPG	UTB30SPG	UTB5SPG	UTB60SPG
Max Continuous Operating Voltage (Uc)	150 VAC 170 VDC	12 VAC 18 VDC	23 VAC 33 VDC	5 VAC 7 VDC	45 VAC 64 VDC
Rated Load Current (IL)	2A	2A	2A	2A	2A
Frequency	3 MHz	1 MHz	2 MHz	0.5 MHz	3 MHz
Loop Resistance	1 Ω	1 Ω	1 Ω	1 Ω	1 Ω
Max Discharge Current (Imax), L+L-PE	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs
Protection Modes	Common Differential	Common Differential	Common Differential	Common Differential	Common Differential
Technology	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)
Voltage Protection Level (Up), L-L	220 V @ 3 kA	25 V @ 3 kA	44 V @ 3 kA	10 V @ 3 kA	85 V @ 3 kA
Connection, Stranded	1 - 4 mm ²	1 - 4 mm ²	1 - 4 mm ²	1 - 4 mm ²	1 - 4 mm ²
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail	35 mm top hat DIN rail	35 mm top hat DIN rail	35 mm top hat DIN rail
Temperature	-20 to 65 °C	-20 to 65 °C	-20 to 65 °C	-20 to 65 °C	-20 to 65 °C
Enclosure Material	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20 NEMA®-1	IP 20 NEMA®-1	IP 20 NEMA®-1	IP 20 NEMA®-1	IP 20 NEMA®-1
Depth (D)	72mm	72mm	72mm	72mm	72mm
Height (H)	90 mm	90 mm	90 mm	90 mm	90 mm
Width (W)	12 mm	12 mm	12 mm	12 mm	12 mm
Unit Weight	0.07 kg	0.07 kg	0.07 kg	0.07 kg	0.07 kg
Certification Details	UL® 497B	UL® 497B	UL® 497B	UL® 497B	UL® 497B
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C
Replacement Module	UTB110SPGM	UTB15SPGM	UTB30SPGM	UTB5SPGM	UTB60SPGM

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE