

Compact Series 2 Flange Elbow Coupling 15-Degree



Compact Series 2 Flange Elbow Coupling, 15-Degree attaches directly to the enclosure for applications where a vertical tube is not required, enabling 300-degree enclosure rotation and 15-degree angle tilt. Maintenance-free bearing is steel and polyamide. Includes access plate for easy wire installation.

FEATURES

Coupling can rotate 300 degrees with stop

Enclosure is mounted at a 15-degree incline angle

Installation hardware, mounting fasteners and gasket included

Assembled Compact Series 2 HMI Arm System has a max weight load of 101 lb. (45.8 kg)

SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Height	Width	Material	Finish	Color
CCS2FEC15LG	15678	45mm	60mm	Aluminum	Powder Coated	Light Gray

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE