

Concept Adjustable-Depth Mounting Kits



Adjustable-Depth Mounting Kits provide mounting means for installing panels, swing-out panels, DIN rails, rack angles, mounting channels or grid straps at any depth from front to rear of enclosure.

FEATURES

Kits include slide mechanisms and hardware

Use two kits when enclosure has six collar studs for mounting panel

Kit catalog numbers ending in 2 contain two slide mechanisms; catalog numbers ending in 4 contain four slide mechanisms

SPECIFICATIONS

Material: Mild Steel

Finish: Plated

Table 1/1

Catalog Number	Article Number	Fits Depth	Quick Ship
CAM82	78800	203mm min	No
CAM102	41299	254mm min	No
CAM122	78820	305mm min	No
CAM162	14496	406mm min	No
CAM64	78780	152mm min	No
CAM84	78790	203mm min	No
CAM202	14497	508mm min	No
CAM104	41289	254mm min	No
CAM124	78810	305mm min	No
CAM164	14495	406mm min	No
CAM204	14498	508mm min	No

ADDITIONAL PRODUCT DETAILS

Dead Front Panel and Swing-Out Rack Frame cannot be mounted on adjustable mounting kit.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE