

External Data Pocket, Type 4, 4X and 12, 12.00x18.00x3.25, SS Type 304

CATALOG NUMBER

ADPX4CSS



Mounted on the exterior of an enclosure, Data Pockets allow access to system documentation without having to open the enclosure door

INDUSTRY STANDARDS

UL 508A Listed; Type 4, 12; File No. E61997 (MS)

cUL Listed per C22.2 No. 94; Type 4, 12; File No. E61997 (MS)

UL 508A Listed; Type 4, 4X, 12; File No. E61997 (SS)

cUL Listed per C22.2 No. 94; Type 4, 4X, 12; File No. E61997 (SS)

Mild Steel Models:

NEMA/EEMAC Type 4, 12

IEC 60529, IP66

Stainless Steel Models:

NEMA/EEMAC Type 4, 4X, 12

IEC 60529, IP66

FEATURES

Available in mild steel or stainless steel to match the enclosure finish

Foam-in-place gasket to protect documentation from harsh environments

Hinged front for easy access to contents

Three sizes accommodate a wide variety of documents

Sloped top sheds liquids and prevents accumulation of extraneous material

Optional wing knob and keylock inserts available for additional security

Front of pocket hinges away from frame

PRODUCT ATTRIBUTES

Article Number: 16464

Product Family: InterSafe

Material: Stainless Steel 304

Finish: Brushed

Thickness: 1.52mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE