

Grounding Bar System



Three sizes of grounding bars and insulated mounting brackets are available. Bars include M6 and M5 tapped holes to provide a common point for grounding equipment. Fits all enclosures if mounted vertically. See table for horizontal mounting.

INDUSTRY STANDARDS

UL Component Recognized; File No. E61997

FEATURES

Bars are plated copper with M6 and M5 tapped holes; mounting bracket is insulated

Fits all enclosures if mounted vertically; for depth-mounting, 200mm length fits 400mm deep frame, 400mm fits 600mm, and 600mm fits 800mm

Mounting hardware and M5, M6 fasteners for grounding included

SPECIFICATIONS

Thickness: 6.4mm
Finish: Plated

Table 1/1				
Catalog Number	Article Number	Material	Length	Quick Ship
PGS2K	45979	Copper	200mm	No
PGS4K	45989	Copper	400mm	No
PGS6K	45999	Copper	600mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE