

ProLine G2 Fully Sealed Plinth (100mm Solid Base)



No need to use a gland plate in the base of the enclosure with the Fully-Sealed Plinth Base (100mm Solid Base), which includes fully-sealed gland plates on the sides. Solid bases can easily be joined, for convenient cable management in joined/ganged enclosures while maintaining Type 12 environmental rating.

FEATURES

Maintains NEMA 12 rating without requiring gland plate

Two side gland plates for cable management options

Seamless polyurethane gasket (UL component recognized) provides a water-tight, dust-tight seal against moisture and contaminants

Optional Cable Entry Gland Plate for additional cable management solutions

Welded corners

Drill points for locating casters (not included)

Installation hardware included

SPECIFICATIONS

Color: Jet Black
Finish: Powder Coated
Color Code: RAL 9005

Table 1/1

Catalog Number	Article Number	Height	Width	Depth	Material	Thickness
P2B145	30936	100mm	465mm	399mm	Mild Steel	1.52mm
P2B146	30937	100mm	565mm	399mm	Mild Steel	1.52mm
P2B164	30938	100mm	365mm	599mm	Mild Steel	1.52mm
P2B165	30941	100mm	465mm	599mm	Mild Steel	1.52mm
P2B166	30943	100mm	565mm	599mm	Mild Steel	1.52mm
P2B166HF	30942	100mm	565mm	599mm	Mild Steel	1.52mm
P2B168	30944	100mm	765mm	599mm	Mild Steel	1.52mm
P2B1104	30912	100mm	365mm	999mm	Mild Steel	1.9mm
P2B1105	30913	100mm	465mm	999mm	Mild Steel	1.9mm
P2B1106	30915	100mm	565mm	999mm	Mild Steel	1.9mm
P2B1106HF	30914	100mm	565mm	999mm	Mild Steel	1.9mm
P2B1108	30916	100mm	765mm	999mm	Mild Steel	1.9mm
P2B1124	30917	100mm	365mm	1199mm	Mild Steel	1.9mm
P2B1125	30918	100mm	465mm	1199mm	Mild Steel	1.9mm
P2B1126	30921	100mm	565mm	1199mm	Mild Steel	1.9mm
P2B1128	30922	100mm	765mm	1199mm	Mild Steel	1.9mm
P2B1164	30923	100mm	365mm	1599mm	Mild Steel	1.9mm

Catalog Number	Article Number	Height	Width	Depth	Material	Thickness
P2B1165	30924	100mm	465mm	1599mm	Mild Steel	1.9mm
P2B1166	30925	100mm	565mm	1599mm	Mild Steel	1.9mm
P2B1168	30926	100mm	765mm	1599mm	Mild Steel	1.9mm
P2B1184	34068	100mm	365mm	1799mm	Mild Steel	1.9mm
P2B1185	30927	100mm	465mm	1799mm	Mild Steel	1.9mm
P2B1186	30928	100mm	565mm	1799mm	Mild Steel	1.9mm
P2B1188	30931	100mm	765mm	1799mm	Mild Steel	1.9mm
P2B1810	30945	100mm	965mm	799mm	Mild Steel	1.9mm
P2B184	30946	100mm	365mm	799mm	Mild Steel	1.9mm
P2B185	30947	100mm	465mm	799mm	Mild Steel	1.9mm
P2B186	30951	100mm	565mm	799mm	Mild Steel	1.9mm
P2B186HF	30948	100mm	565mm	799mm	Mild Steel	1.9mm
P2B188	30952	100mm	765mm	799mm	Mild Steel	1.9mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE