

## ProLine-PC Doors for Upper Front



Doors fit on the upper front of the PC frame and are hinged on the left side. A 2-point latch system is operated by a Small Flush Bezel with tool-to-open insert located on the lower right side of the door. Other inserts and a Flush Swing Handle are also available. Noted sizes also available in stainless steel.

### FEATURES

---

Doors have foam-in-place gaskets and ground studs

Small Flush Bezel with tool-to-open insert included; other handle options available

## SPECIFICATIONS

**Thickness:** 1.9mm  
**Color:** Light Gray  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1

| Catalog Number | Article Number | Material   | Fits PC Frame | Quick Ship |
|----------------|----------------|------------|---------------|------------|
| PDST88PC       | 98410          | Mild Steel | 1600 x 800mm  | No         |
| PDST96PC       | 98420          | Mild Steel | 1800 x 600mm  | No         |
| PDST108PC      | 98450          | Mild Steel | 2000 x 800mm  | No         |
| PDST106PC      | 98440          | Mild Steel | 2000 x 600mm  | No         |
| PDST98PC       | 98430          | Mild Steel | 1800 x 800mm  | No         |
| PDST86PC       | 98400          | Mild Steel | 1600 x 600mm  | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**