

ProLine-PC Window Door for Upper and Lower Front



Window Doors include foam-in-place gaskets provided for door and window seals. Window is .25-in.-thick and available in clear safety glass or gray-tint polycarbonate. Doors are hinged on the left. Hidden hinges have retained hinge pins. Window door has a 2-point latch system and a Small Flush Bezel with tool-to-open insert. Other inserts and a Flush Swing Handle also are available.

FEATURES

Window door has a 2-point latch system and a Small Flush Bezel with tool-to-open insert

Seamless foam in place gasket

SPECIFICATIONS

Thickness: 2.3mm

Table 1/1						
Catalog Number	Article Number	Material	Window Size	Window Material	Color	Color Code
PDW86	89380	Aluminum	646 x 645mm, 645 x 446mm	Polycarbonate	Light Gray	RAL 7035
PDWG86	98690	Aluminum	645 x 446mm	Safety Glass, Glass	Light Gray	RAL 7035

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE