

Swing-Out Panel



Swing-Out Panels allow a front-mounted panel to pivot out of an enclosure frame opening. This accessory includes a panel and all the necessary hardware. Panels provide 170 degrees of rotation, with the capability to hinge from the right or left side.

FEATURES

Swing-Out Panels are available for 600-, 700- and 800-mm wide enclosures

Spring-loaded pivot post allows for easy installation

Hinge blocks are anodized black; supports and panel have a painted white finish

Quarter-turn latches are provided to secure the Swing-Out Panel in the closed position

Panels provide 170 degrees of rotation, with the capability to hinge from the right or left side.

All necessary mounting hardware included

SPECIFICATIONS

Thickness: 2.66mm
Finish: Powder Coated
Color: White

Table 1/1

Catalog Number	Article Number	Material	Fits Frame Width	Quick Ship
PSP146	91260	Mild Steel	600mm	No
PSP148	91920	Mild Steel	800mm	No
PSP168	91930	Mild Steel	800mm	No
PSP186	91280	Mild Steel	600mm	No
PSP188	91940	Mild Steel	800mm	No
PSP206	91830	Mild Steel	600mm	No
PSP208	91950	Mild Steel	800mm	No
PSP226	91840	Mild Steel	600mm	No
PSP228	91960	Mild Steel	800mm	No
PSP76	91250	Mild Steel	600mm	No
PSP78	91910	Mild Steel	800mm	No
PSP147	91860	Mild Steel	700mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE