

Elbow 30-Degree Sweep Lay-in Painted Galvanized

Power Utilities

Lay-in Painted Galvanized 30-Degree Sweep Elbows are used for large radius turns.



FEATURES

Lay-in Painted Galvanized 30-Degree Sweep Elbows are used for large radius turns

SPECIFICATIONS

Color Code: ANSI 61

Color: Gray

Table 1/2

Catalog Number	Article Number	Type	Height	Width	Material	Finish
F44T3R30SE	43559	Elbow	102 mm	102 mm	Mild Steel	Powder Coated
F66T3R30SE	43709	Elbow	152 mm	152 mm	Mild Steel	Powder Coated
F88T3R30SE	43869	Elbow	203 mm	203 mm	Mild Steel	Powder Coated

Table 2/2

Catalog Number	Article Number	Thickness
----------------	----------------	-----------

F44T3R30SE	43559	1.52 mm
F66T3R30SE	43709	1.52 mm
F88T3R30SE	43869	1.9 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE