

MI Series Alloy 825 XMI-A HAx Heating Cable



nVent RAYCHEM XMI-A mineral insulated (MI) series resistance trace heating cables provide freeze protection and process temperature maintenance on pipes/vessels up to 1022 °F/550 °C and intermittent exposure to 1200 °F/650 °C. Available with 300 V and 600 V rating, approved for applications up to 61 W/ft (200 W/m) and hazardous areas. The Alloy 825 sheath provides extreme resistance to a broad range of corrosive environments.

FEATURES

Reliable during long life: 10 year product warranty available, robust and rugged construction, proven in harsh climates extends life expectancy

Reduced total installed cost

Dual conductor versions particularly suited to small pipes and instrument tubing

Reduced power supply costs: lower start up currents compared with other technologies

Simple controls: current monitoring on series resistance provides instant visibility on critical circuits

Fast track / expedite service for configured heating units for eligible designs

Excellent corrosion resistance to a wide range of organic acids, alkalis and chloride stress-corrosion cracking

SPECIFICATIONS

Max Continuous Exposure Temperature, Power Off:	650 °C
Min Installation Temperature:	-60 °C
Sheath Material:	Alloy 825
Area Classification:	Non-Hazardous; Hazardous
Insulation Material:	Magnesium Oxide
Ground Path Type:	Sheath
Conductor Material:	Various Alloys and Copper

Table 1/1

Catalog Number	Supply Voltage	Max Power Output	Conductor Quantity	Nominal Resistance @ 20°C	Outer Diameter
----------------	----------------	------------------	--------------------	---------------------------	----------------

61SC6640	0 – 600 V	200 W/m	1	2 Ω/km	8.1 mm
61SC5102	0 – 600 V	200 W/m	1	3.3 Ω/km	6.4 mm
62SC5128	0 – 600 V	270 W/m	2	4.3 Ω/km	13.8 mm
61SC5162	0 – 600 V	200 W/m	1	5.3 Ω/km	6.8 mm
62SC5204	0 – 600 V	270 W/m	2	6.6 Ω/km	12.6 mm
61SC5258	0 – 600 V	200 W/m	1	8.5 Ω/km	5.5 mm
62SC5324	0 – 600 V	270 W/m	2	10.5 Ω/km	10.2 mm
61SC5409	0 – 600 V	200 W/m	1	13.5 Ω/km	4.9 mm
62SC5516	0 – 600 V	270 W/m	2	17 Ω/km	9.2 mm
61SC5651	0 – 600 V	200 W/m	1	21.3 Ω/km	4.7 mm
62SC5818	0 – 600 V	270 W/m	2	27 Ω/km	8.4 mm
61SP4113	0 – 600 V	200 W/m	1	37 Ω/km	4.7 mm
62SC4130	0 – 600 V	270 W/m	2	43 Ω/km	7.7 mm
61SP4145	0 – 600 V	200 W/m	1	48 Ω/km	4.3 mm
61SP4183	0 – 600 V	200 W/m	1	60 Ω/km	4.3 mm
62SC4200	0 – 600 V	270 W/m	2	66 Ω/km	7.2 mm
61SP4231	0 – 600 V	200 W/m	1	76 Ω/km	4.4 mm
62SP4281	0 – 600 V	270 W/m	2	92 Ω/km	7.4 mm
61SP4290	0 – 600 V	200 W/m	1	95 Ω/km	4.5 mm

32SC4324	0 – 300 V	200 W/m	2	105 Ω/km	4.7 mm
32SA2400	0 – 300 V	200 W/m	2	13200 Ω/km	3.7 mm
61SP4366	0 – 600 V	200 W/m	1	120 Ω/km	4.4 mm
32SA2275	0 – 300 V	200 W/m	2	9000 Ω/km	3.9 mm
32SF1110	0 – 300 V	200 W/m	2	36000 Ω/km	4 mm
32SB2114	0 – 300 V	200 W/m	2	3750 Ω/km	4.4 mm
32SB3700	0 – 300 V	200 W/m	2	2300 Ω/km	4.3 mm
32SB3914	0 – 300 V	200 W/m	2	3000 Ω/km	4.1 mm
61SB3150	0 – 600 V	200 W/m	1	500 Ω/km	4.3 mm
61SB3200	0 – 600 V	200 W/m	1	660 Ω/km	4.6 mm
62SB3700	0 – 600 V	270 W/m	2	2300 Ω/km	6.7 mm
62SB3914	0 – 600 V	270 W/m	2	3000 Ω/km	5.9 mm
62SP4402	0 – 600 V	270 W/m	2	130 Ω/km	7 mm
32SF2750	0 – 300 V	200 W/m	2	24500 Ω/km	4 mm
32SA2600	0 – 300 V	200 W/m	2	19700 Ω/km	4.1 mm
32SF2900	0 – 300 V	200 W/m	2	29500 Ω/km	4.1 mm
61SA2130	0 – 600 V	200 W/m	1	4300 Ω/km	4.1 mm
61SA2100	0 – 600 V	200 W/m	1	3300 Ω/km	4.1 mm
61SA3700	0 – 600 V	200 W/m	1	2300 Ω/km	4.1 mm

32SQ3200	0 – 300 V	200 W/m	2	660 Ω/km	4.1 mm
61SA2160	0 – 600 V	200 W/m	1	5250 Ω/km	4.1 mm
32SP4458	0 – 300 V	200 W/m	2	150 Ω/km	4.8 mm
61SP4467	0 – 600 V	200 W/m	1	155 Ω/km	4.3 mm
61SA3850	0 – 600 V	200 W/m	1	2800 Ω/km	4.3 mm
61SQ4732	0 – 600 V	200 W/m	1	240 Ω/km	4.3 mm
61ST3280	0 – 600 V	200 W/m	1	920 Ω/km	4.3 mm
32SA2170	0 – 300 V	200 W/m	2	5600 Ω/km	4.2 mm
32SA2200	0 – 300 V	200 W/m	2	6600 Ω/km	4.3 mm
32SF1180	0 – 300 V	200 W/m	2	59000 Ω/km	4.4 mm
32SQ3150	0 – 300 V	200 W/m	2	495 Ω/km	4.3 mm
61SA3500	0 – 600 V	200 W/m	1	1640 Ω/km	4.3 mm
32SA2318	0 – 300 V	200 W/m	2	10400 Ω/km	4.4 mm
61SA2200	0 – 600 V	200 W/m	1	6565 Ω/km	4.3 mm
61SQ3118	0 – 600 V	200 W/m	1	390 Ω/km	4.4 mm
61SQ4581	0 – 600 V	200 W/m	1	190 Ω/km	4.4 mm
32SP4734	0 – 300 V	200 W/m	2	240 Ω/km	4.4 mm
32SQ3472	0 – 300 V	200 W/m	2	1560 Ω/km	4.5 mm
32SQ3293	0 – 300 V	200 W/m	2	965 Ω/km	4.5 mm

32SP4583	0 – 300 V	200 W/m	2	190 Ω/km	4.5 mm
32SQ3374	0 – 300 V	200 W/m	2	1240 Ω/km	4.6 mm
62SP4561	0 – 600 V	270 W/m	2	185 Ω/km	6.7 mm
32SQ3100	0 – 300 V	200 W/m	2	330 Ω/km	4.7 mm
62SF1110	0 – 600 V	270 W/m	2	36000 Ω/km	4.9 mm
62SF2900	0 – 600 V	270 W/m	2	29500 Ω/km	4.9 mm
62SF2750	0 – 600 V	270 W/m	2	24500 Ω/km	5.2 mm
62SQ3374	0 – 600 V	270 W/m	2	1240 Ω/km	5.5 mm
62ST2115	0 – 600 V	270 W/m	2	3750 Ω/km	5.5 mm
62SQ3505	0 – 600 V	270 W/m	2	1670 Ω/km	5.5 mm
62SP4775	0 – 600 V	270 W/m	2	255 Ω/km	6.4 mm
62SQ3286	0 – 600 V	270 W/m	2	940 Ω/km	5.6 mm
62SA2275	0 – 600 V	270 W/m	2	9000 Ω/km	5.7 mm
62SF2600	0 – 600 V	270 W/m	2	19700 Ω/km	5.8 mm
62SQ3150	0 – 600 V	270 W/m	2	495 Ω/km	5.8 mm
62SQ3200	0 – 600 V	270 W/m	2	660 Ω/km	5.8 mm
62SA2170	0 – 600 V	270 W/m	2	5600 Ω/km	6.1 mm
62SA2414	0 – 600 V	270 W/m	2	13600 Ω/km	6.1 mm
62SF2200	0 – 600 V	270 W/m	2	6600 Ω/km	6.2 mm

62SQ3100	0 – 600 V	270 W/m	2	330 Ω/km	6.5 mm
62ST3505	0 – 600 V	270 W/m	2	1760 Ω/km	5.5 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT