

Telescopic Slide Slim Line, Length 559 mm

CATALOG NUMBER

60110-440



Narrow Telescopic Slide for Subracks with > 100 % extension.

CERTIFICATIONS



FEATURES

Suitable for 84 HP width subracks (type F, type H, type L)
Locks at full extension
Hinged
Extension length > 100 %
Rail width 7.5 mm
Maximum clear width of extension/drawer w = 84 HP (435 mm)

PRODUCT ATTRIBUTES

Length: 559mm
Package Quantity: 2
Finish: Zinc Plated
Material: Steel
Product Type: Telescopic Slide
Static Load: 15kg
Type: Narrow
Net Weight: 2.123kg

ADDITIONAL PRODUCT DETAILS

To mount on 19" plane please order assembly kit separately.

Telescopic slight can only be assembled to a subrack without an assembled rear angle or a modified rear angle (with special cutout).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE