

# RackChiller In-Row 45



RackChiller In-Row Coolers (IRC) are designed to deliver localized/supplemental energy efficient cooling in data centers. The RackChiller In-Row 45 air-to liquid cooler is a modular and scalable precision cooling solution that can replace or supplement traditional data center cooling infrastructure. The units can be scaled optimally to suit individual packaging density and redundancy requirements.

The cooling system is integrated into a Varistar CP mobile frame for ideal side by side connection to Varistar CP or third party racks. The cooler comes with perforated front and rear doors. This allows seamless integration into rows of racks with hot or cold aisle containment. The integrated fans move the warm exhaust air from the hot aisle through an air to water heat exchanger where the heat is transferred to a water circuit. The air is then provided into the cold aisle towards the equipment.

## FEATURES

In-Row air/liquid cooler, ideal for hot aisle containment

Hot-swappable components simplify repair and maximize availability

Designed for efficient operation at increased facility water temperatures

Combination with direct to chip liquid cooling

Modular standard - easy to adapt to individual requirements.

Minimum changes between In-Row and LHX+ (In-Rack) design - simplifies planning, layout and specification

Fans, power supplies, controller and control valve all are hot-swappable

Automatic fan speed and valve opening control

7" high resolution touch screen interface

Hydraulic and electric connection through top or bottom

Monitoring via Ethernet interface (Web browser, Modbus TCP, SNMP v2c) and Modbus RTU

## SPECIFICATIONS

Table 1/3

Catalog Number	Product Type	Product Family	Width	Depth	Height	Supply Voltage
10630-103	Air/Liquid Heat Exchanger	RackChiller	300mm	1200mm	2000mm	200 – 240V

CatalogNumber	Product Type	Product Family	Width	Depth	Height	Supply Voltage
10630-102	Air/Liquid Heat Exchanger	RackChiller	300mm	1000mm	2000mm	200 – 240V

Table 2/3

Catalog Number	Coolant Feed	Finish	Material	Package Quantity	Protection Rating	Rack Height
10630-103	Top, Bottom	Powder Coated	Steel	1	IP20	42U
10630-102	Top	Powder Coated	Steel	1	IP20	42U

Table 3/3

Catalog Number	Quick Ship
10630-103	No
10630-102	No

## ADDITIONAL PRODUCT DETAILS

---

For trouble-free operation of the air/liquid heat exchanger the quality requirements of the coolant must be maintained; The selection of appropriate anti-corrosion and frost protection agents depends on the environment in which the unit is used and on the external chiller

At coolant temperatures below 14 °C, there is an increased risk of condensation. We recommend using a condensate management package

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**