


RatiopacPRO 19" Mounting Bracket With Handle, Retrofitting



With this 19" mounting bracket with handles the flexible and robust RatiopacPRO/-AIR case, is simple to convert from desktop to 19" rack-mountable.

CERTIFICATIONS



FEATURES

For conversion of cases with cover strip, front handle or 19" mounting bracket

SPECIFICATIONS

Material: Aluminum
Product Type: Handle
Type: Static

Table 1/2

Catalog Number	Package Quantity	Handle Type	Color	Finish	Product Family	Works With
24572-700	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO

CatalogNumber	Package Quantity	Handle Type	Color	Finish	Product Family	Works With
24572-701	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO
24572-702	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO
24572-705	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO AIR	Cases, RatiopacPRO AIR
24572-704	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO	Cases, RatiopacPRO
24572-707	2	Front Handle with 19" Mounting Brackets	Dark Grey	Powder Coated	RatiopacPRO AIR	Cases, RatiopacPRO AIR

Table 2/2

Catalog Number	Quick Ship
24572-700	No
24572-701	No
24572-702	No
24572-705	No
24572-704	No
24572-707	No

ADDITIONAL PRODUCT DETAILS

No slide rails may be used when fitting into cabinets or 19" cases.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE