nVent | SCHROFF

We connect and protect

Varistar CP IP 20 Cabinet, Glass Front Door, Steel Rear Door

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FEATURES

- Type of protection IP 20
- With glass front door
- Doors with single point locking, side panels with quick release fastener
- Static load-carrying capacity 1600 kg

SPECIFICATIONS

Product Type: Cabinet

Protection Rating: IP20

Material: Steel

Table 1/3

Catalog Number	Rack Height	Height	Frame Color	Width	Frame Color Code	Cladding Material
10630-040	42U	2000mm	Black Grey	600mm	RAL 7021	Steel
10630-038	38U	1800mm	Black Grey	600mm	RAL 7021	Steel

CatalogNumber	Rack Height	Height	Frame Color	Width	Frame Color Code	Cladding Material
10630-039	42U	2000mm	Black Grey	600mm	RAL 7021	Steel
10630-037	38U	1800mm	Black Grey	600mm	RAL 7021	Steel

Table 2/3

Catalog Number	Depth	Cladding Color	Package Quantity	Cladding Color Code	Complies With	Finish
10630-040	600mm	Black Grey	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Powder Coated
10630-038	800mm	Black Grey	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Powder Coated
10630-039	600mm	Black Grey	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Powder Coated
10630-037	600mm	Black Grey	1	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Powder Coated

Table 3/3

Catalog Number	Frame Material	Static Load	Quick Ship
10630-040	Steel	1600kg	No
10630-038	Steel	1600kg	No
10630-039	Steel	1600kg	No
10630-037	Steel	1600kg	No

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to the doors.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.