


DIN Rail

Data Solutions

A DIN rail is a standard metal rail widely used for mounting circuit breakers and industrial control equipment inside equipment racks.



FEATURES

Pre-Cut Lengths and with Perforations

Steel with electrogalvanized finishing

Comply with: EN 60715 Standards

SPECIFICATIONS

Product Type: DIN Rail

Table 1/2

Catalog Number	Material	Height	Length	Finish	Package Quantity	Depth
20118-872	Steel	35mm	125mm	Zinc Plated	4	15mm
20118-873	Steel	35mm	175mm	Zinc Plated	4	15mm
20118-874	Steel	35mm	275mm	Zinc Plated	4	15mm
20118-875	Steel	35mm	375mm	Zinc Plated	4	15mm
20118-876	Steel	35mm	475mm	Zinc Plated	4	15mm

CatalogNumber	Material	Height	Length	Finish	Package Quantity	Depth
20118-877	Steel	35mm	575mm	Zinc Plated	4	15mm
20118-878	Steel	35mm	125mm	Zinc Plated	4	7.5mm
20118-879	Steel	35mm	175mm	Zinc Plated	4	7.5mm
20118-880	Steel	35mm	275mm	Zinc Plated	4	7.5mm
20118-881	Steel	35mm	375mm	Zinc Plated	4	7.5mm
20118-882	Steel	35mm	475mm	Zinc Plated	4	7.5mm
20118-883	Steel	35mm	575mm	Zinc Plated	4	7.5mm
20118-890	Steel	35mm	125mm	Zinc Plated	10	7.5mm
20118-891	Steel	35mm	175mm	Zinc Plated	10	7.5mm
20118-892	Steel	35mm	275mm	Zinc Plated	10	7.5mm
20118-893	Steel	35mm	375mm	Zinc Plated	10	7.5mm
20118-894	Steel	35mm	475mm	Zinc Plated	10	7.5mm
20118-895	Steel	35mm	575mm	Zinc Plated	10	7.5mm
20118-884	Steel	35mm	125mm	Zinc Plated	10	15mm
20118-885	Steel	35mm	175mm	Zinc Plated	10	15mm
20118-886	Steel	35mm	275mm	Zinc Plated	10	15mm
20118-887	Steel	35mm	375mm	Zinc Plated	10	15mm
20118-888	Steel	35mm	475mm	Zinc Plated	10	15mm

CatalogNumber	Material	Height	Length	Finish	Package Quantity	Depth
20118-889	Steel	35mm	575mm	Zinc Plated	10	15mm

Table 2/2

Catalog Number	Width
20118-872	125mm
20118-873	175mm
20118-874	275mm
20118-875	375mm
20118-876	475mm
20118-877	575mm
20118-878	125mm
20118-879	175mm
20118-880	275mm
20118-881	375mm
20118-882	475mm
20118-883	575mm
20118-890	125mm
20118-891	175mm
20118-892	275mm
20118-893	375mm

Catalog Number	Width
20118-894	475mm
20118-895	575mm
20118-884	125mm
20118-885	175mm
20118-886	275mm
20118-887	375mm
20118-888	475mm
20118-889	575mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE