

# Varistar CP Steel Door, Perforated With 3-Point Locking

## Data Solutions



Varistar CP perforated steel door, IP 20 with three point locking.

### FEATURES

Perforated steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

### SPECIFICATIONS

<b>Locking Type:</b>	3-Point Locking
<b>Product Type:</b>	Cabinet Door
<b>Protection Rating:</b>	IP20
<b>Material:</b>	Steel

Table 1/2

Catalog Number	Rack Height	Height	Width	Package Quantity	Color	Color Code
21630-101	42U	2000mm	800mm	1	Black Grey	RAL 7021
21630-099	47U	2200mm	600mm	1	Black Grey	RAL 7021

CatalogNumber	Rack Height	Height	Width	Package Quantity	Color	Color Code
21630-426	29U	1400mm	600mm	1	Black Grey	RAL 7021
21630-427	29U	1400mm	800mm	1	Black Grey	RAL 7021
21630-425	24U	1200mm	800mm	1	Black Grey	RAL 7021
21630-428	33U	1600mm	600mm	1	Black Grey	RAL 7021
21630-424	24U	1200mm	600mm	1	Black Grey	RAL 7021
21630-429	33U	1600mm	800mm	1	Black Grey	RAL 7021
21630-103	52U	2450mm	800mm	1	Black Grey	RAL 7021
21630-430	38U	1800mm	600mm	1	Black Grey	RAL 7021
21630-100	52U	2450mm	600mm	1	Black Grey	RAL 7021
21630-102	47U	2200mm	800mm	1	Black Grey	RAL 7021
21630-431	38U	1800mm	800mm	1	Black Grey	RAL 7021
21630-098	42U	2000mm	600mm	1	Black Grey	RAL 7021

Table 2/2				
Catalog Number	Complies With	Finish	Type	Works With
21630-101	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-099	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-426	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-427	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-425	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP

Catalog Number	Complies With	Finish	Type	Works With
21630-428	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-424	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-429	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-103	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-430	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-100	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-102	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-431	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP
21630-098	IEC 61587-1, IEC 61587-3	Powder Coated	Steel Door, Perforated	Varistar CP

## ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**