

Prefabricated Cable Assembly



Safe 24 V operating low-voltage cable assembly is of simple design and rugged construction to ensure long life and minimum maintenance. The self-regulating feature enables the heating system to vary power output in response to changes in surrounding temperatures and weather conditions. As temperatures increase, the self-regulating cable automatically decreases its heat output, providing dependable over temperature protection. Self-regulating cables conserve energy by providing heat when and where it is needed over the entire circuit length. Available cable assemblies include 12 m (39.4') of regular electrical cable connected in our manufacturing facilities to self-regulating cable.

FEATURES

Self-regulating heating technology from nVent RAYCHEM

Touch-safe operating temperature

Prefabricated and tested in factory

Designed for installation into mounting channel

Rugged construction to withstand harsh environmental conditions

SPECIFICATIONS

Material: Copper;Fluoropolymer

Finish: Nickel Plated

Table 1/1

Catalog Number	Length 1	Length 2	Operating Voltage	Temperature	Number of Conductors
RHS4TA4CA12	4 m	12 m	24 V	80 °C Max	2
RHS4TA6CA12	6 m	12 m	24 V	80 °C Max	2
RHS4TA7CA12	7 m	12 m	24 V	80 °C Max	2
RHS4TA9CA12	9 m	12 m	24 V	80 °C Max	2

ADDITIONAL PRODUCT DETAILS

Length 1 represents the length of self-regulated heating cable. Length 2 represents the length of electrical cable.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE