


# RRCBI Insulated Round Braid in Coil, Plain Copper



## CERTIFICATIONS



## FEATURES

Braids in coil are mainly used for power distribution or earthing applications

Non-magnetic material

## SPECIFICATIONS

**Material:** Copper;Polyvinylchloride

Table 1/2

| Catalog Number | Article Number | Nominal Current | Cross Section     | Number of Wires | Wire Diameter | Length |
|----------------|----------------|-----------------|-------------------|-----------------|---------------|--------|
| RRCBI15-10     | 510500         | 75A             | 10mm <sup>2</sup> | 560             | 0.15mm        | 25m    |
| RRCBI15-16     | 510510         | 120A            | 16mm <sup>2</sup> | 900             | 0.15mm        | 25m    |

Table 2/2

| Catalog Number | Article Number | Diameter | Unit Weight |
|----------------|----------------|----------|-------------|
| RRCBI15-10     | 510500         | 7 mm     | 0.1 kg      |
| RRCBI15-16     | 510510         | 8 mm     | 0.16 kg     |

**Insulation Thickness:** 1 mm

**Insulation Voltage:** 450V

**Flammability Rating:** UL® 94V-0

**Temperature:** 70 °C Max

## ADDITIONAL PRODUCT DETAILS

Unit weight is per meter (3.28').

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE