We connect and protect

EuropacPRO 19" Subrack Kit for DIN Connector, Slide Rail, Retrofit Shielding

Power Utilities

Non-shielded subrack for Din Connector mounting EN 60603-2 , Subrack can be assembeld on slide rails to support the subrack inside a cabinet.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- Subrack with side panel type F ("flexible"), 19" bracket with notch for slide rail assembly
- Installed load up to 11 kg
- Subrack can be used with slide rails
- Horizontal rails, rear, for connector mounting (IEC 60603-2 / DIN 41612)
- Threaded insert pre-fitted

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-192	3 U	235 mm	1	DIN Connector	160 mm, 220 mm	Stainless Steel

CatalogNumber	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-193	3 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Stainless Steel
24553-194	3 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel
24553-492	6 U	235 mm	1	DIN Connector	160 mm, 220 mm	Stainless Steel
24553-493	6 U	295 mm	1	DIN Connector	160 mm, 220 mm, 280 mm	Stainless Steel
24553-494	6 U	355 mm	1	DIN Connector	160 mm, 220 mm, 280 mm, 340 mm	Stainless Steel

Table 2/3

Catalog Number	Handle Included	Mounting	Complies With	EMC Shielding	Product Type	Rack Width
24553-192	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-193	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-194	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-492	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-493	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP
24553-494	No	Rack	IEC 60297-3-103	No	Subrack/Chassis	84 HP

Table 3/3

Catalog Number	Static Load
24553-192	11 kgf
24553-193	11 kgf
24553-194	11 kgf
24553-492	11 kgf

Catalog Number	Static Load
24553-493	11 kgf
24553-494	11 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.