

# Front Panel, Flat, With Slot for Stainless Steel EMC Gasket

## Power Utilities

Front panel, flat, with slot for stainless steel EMC gasket.

### CERTIFICATIONS



### FEATURES

Flat front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For stainless steel gasket

### SPECIFICATIONS

Table 1/2						
Catalog Number	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish	Treated Edges
30846-682	63 HP	1	Screw-on Front			
30846-681	42 HP	1	Screw-on Front	Anodized	Conductive	No

Table 2/2						
Catalog Number	Height	Material	Product Type	Rack Height	Type	Width
30846-682	172.9 mm	Aluminum	Front Panel	4 U	Front Panel without Handle	319.7 mm
30846-681	172.9 mm	Aluminum	Front Panel	4 U	Front Panel without Handle	213 mm

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**