

Inpac Front Panel

The front panel can be assembled on to the Inpac Case.



CERTIFICATIONS



FEATURES

Al panel, 2.5 mm

SPECIFICATIONS

Depth:	2.5mm
Material:	Aluminum
Finish:	Anodized
Works With:	Cases
Accessory Type:	Front panel
Product Type:	Front Panel
Product Family:	Inpac

Table 1/2

Catalog Number	Rack Height	Package Quantity	Front Finish	Rear Finish	Treated Edges	EMC Shielding
30828-055	2U	1	Anodized	Anodized	No	No
30828-058	3U	1	Anodized	Anodized	No	No
30828-061	4U	1	Anodized	Anodized	No	No

CatalogNumber	Rack Height	Package Quantity	Front Finish	Rear Finish	Treated Edges	EMC Shielding
30828-067	6U	1	Anodized	Anodized	No	No

Table 2/2			
Catalog Number	Height	Width	Quick Ship
30828-055	76mm	437mm	No
30828-058	120.5mm	437mm	No
30828-061	165mm	437mm	No
30828-067	253.8mm	437mm	No

ADDITIONAL PRODUCT DETAILS

The assembly kit for the front panel is included with the 19" chassis.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE