

801 Standard Pipe Stay



FEATURES


Used for water, heat or gas lines


SPECIFICATIONS

Finish: Epoxy Powder Coated

Material: Steel

Table 1/1					
Catalog Number	Outer Diameter (OD)	Copper Tube Size	Hole Size (HS)	A	В
801125150EP	44 mm	1 1/2"	7.9 mm	107.95 mm	76.2 mm
801075100EP	29.6 mm	1"	7.9 mm	65.09 mm	50.8 mm
801150000EP	49.6 mm		7.9 mm	107.95 mm	76.2 mm
801050075EP	23.4 mm	3/4"	7.9 mm	57.15 mm	44.45 mm
801037050EP	17.4 mm	1/2"	7.9 mm	57.15 mm	44.45 mm
801100125EP	36 mm	1 1/4"	7.9 mm	65.09 mm	50.8 mm





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF

TRACHTE

