

B18-MCS Box/MC/AC Cable Hanger



The nVent CADDY B18-MCS Box/MC/AC Cable Hanger presents an efficient and secure solution for the installation of electrical boxes and conduit in overhead applications by streamlining the process with a single-threaded rod drop. The system is designed to provide greater efficiency in the field with our class-leading range of nVent CADDY Conduit Clamps.

FEATURES

Scoreline breakaway feature can be easily modified by hand while maintaining UL listing

Properly spaces MC/AC cable to help eliminate bundling

Neatly isolates, supports and secures MC/AC cables

Labor and time savings due to built-in first means of support for conduit and/or MC/AC cable

NEC® and CEC compliant

SPECIFICATIONS


Table 1/2

Catalog Number	Material	Finish	Outer Diameter (OD)	Cable Capacity	Hole Size (HS)	Hole Type
MCS50B18A	Steel	Electrogalvanized	10.9 - 14.2 mm	4	6.4 mm	Plain

Table 2/2

Catalog Number	Length (L)	Width (W)
MCS50B18A	457.2mm	58.42 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

