

Cable Spool, Stainless Steel



FEATURES

Cut to length as needed

Pre-stretched restraint cable

Certified chemically compatible with CPVC piping systems

SPECIFICATIONS

Static Load Safety Factor: 1.5:1

Material: Stainless Steel 316 (EN 1.4401)

Table 1/1

Catalog Number	Brace Size	Diameter	Cable Length	Static Load
CSB12CBLSS	#12	2.4 mm	76.2m	1410N
CSB18CBLSS	#18	3.2 mm	76.2m	2750N
CSB36CBLSS	#36	4.8 mm	76.2m	5860N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

