

Clevis Bolt Spacer



FEATURES

Seismically braces the 401 Clevis Hanger series for lateral load

Retrofit ability allows the spacer to be installed after the clevis and pipe are installed

Ears easily pinch closed around the clevis hanger cross bolt with pliers

FM® Specification Tested (up to 8" Pipe Size)

SPECIFICATIONS

Finish: Electrogalvanized


Material: Steel

Table 1/1

Catalog Number	Width (W)	Height (H)	Thickness (T)	Depth (D)
CSBCS0100	30.7 mm	13 mm	1.9 mm	13mm
CSBCS0125	39.4 mm	13 mm	1.9 mm	13mm
CSBCS0150	43.4 mm	13 mm	1.9 mm	13mm
CSBCS0200	57.9 mm	13 mm	1.9 mm	13mm
CSBCS0250	70.6 mm	17 mm	1.9 mm	16.5mm

Catalog Number	Width (W)	Height (H)	Thickness (T)	Depth (D)
CSBCS0300	86.6 mm	17 mm	1.9 mm	16.5mm
CSBCS0350	99.3 mm	17 mm	1.9 mm	16.5mm
CSBCS0400	112 mm	17 mm	1.9 mm	16.5mm
CSBCS0500	139.7 mm	24.9 mm	1.9 mm	22.9mm
CSBCS0600	166.6 mm	24.9 mm	1.9 mm	22.9mm
CSBCS0800	217.4 mm	31 mm	1.9 mm	27.7mm
CSBCS1000	267.2 mm	31 mm	1.9 mm	27.7mm
CSBCS1200	318 mm	31 mm	1.9 mm	27.7mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

