

Deck Screw



FEATURES

Secures nVent CADDY Pyramid Rooftop Anchors to various roof substrate materials

SPECIFICATIONS

Color: Black
Finish: Epoxy Coated
Material: Steel

Table 1/1

Catalog Number	Screw Diameter	Screw Length
A927W001P100	14	50.8mm
A927W008P100	15	50.8mm
A927W002P100	14	76.2mm
A927W009P100	15	76.2mm
A927W003P100	14	101.6mm
A927W010P100	15	101.6mm

Catalog Number	Screw Diameter	Screw Length
A927W004P100	14	127mm
A927W011P100	15	127mm
A927W005P100	14	152.4mm
A927W012P100	15	152.4mm
A927W006P100	14	177.8mm
A927W013P100	15	177.8mm
A927W007P100	14	203.2mm
A927W014P100	15	203.2mm
A927W019P100	15	228.6mm
A927W016P100	14	254mm
A927W020P100	15	254mm
A927W018P100	14	305mm
A927W021P100	15	305mm
A927W022P100	15	355.6mm

ADDITIONAL PRODUCT DETAILS

#14 deck screws are for general purpose use.

#15 deck screws are specially suited for OSB and light gauge steel.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

