

Improved nVent CADDY Cat HP J-Hook Mod Clip with Pedestal Clamp



Improved nVent CADDY Cat HP Mod Clip J-Hook with Pedestal Clamp simplifies installation to pedestals under raised floors. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

CERTIFICATIONS



FEATURES

Listed for use with flexible conduit, cable, or tubing

Requires no screws, rivets or special tools for assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY

SPECIFICATIONS

Finish: Electrogalvanized;nVent CADDY Armour


Material: Steel;Spring Steel

Table 1/1

Catalog Number	Pedestal Size	Static Load
CATHPMCD3B	38.1 mm Round	
CATHPMCD2.5B	28.57 mm Square	

Catalog Number	Pedestal Size	Static Load
CATHPMCD0B	19.05 mm Round	
CATHPMCD1B	19 mm Square, 25 mm Round	70N
CATHPMCD2B	22.22 mm Square	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

