

nVent CADDY Cablecat J-Hook with Hammer-On Flange Clip, Swivel



CERTIFICATIONS



FEATURES

Hammer-on beam clamp with attached nVent CADDY Cablecat J-Hook

Supports low voltage cables

Rotates 360 degrees to support various directional runs of cable

SPECIFICATIONS

Finish: Pregalvanized;nVent CADDY Armour


Material: Steel;Spring Steel

Table 1/1

Catalog Number	Diameter (Ø)	Flange Thickness (FT)
CAT1224	19 mm	3 - 6 mm
CAT1258	19 mm	8 - 12 mm

Catalog Number	Diameter (Ø)	Flange Thickness (FT)
CAT12912	19 mm	14 - 19 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

