


nVent CADDY Cat HP Double J-Hook with BC200 Beam Clamp, Swivel



FEATURES

Low-profile configuration providing double J-Hook capacity

Easy installation to beam flanges

Rotates 360 degrees to support various directional runs of cable

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

SPECIFICATIONS

Finish: Pregalvanized;Electrogalvanized

Material: Steel

Table 1/1

Catalog Number	Diameter (Ø)	Flange Thickness (FT)	Width (W)	A	Static Load
CAT21HPD1BC2	33.3 mm	16 mm Max	130.2 mm	123.8 mm	440N

Catalog Number	Diameter (Ø)	Flange Thickness (FT)	Width (W)	A	Static Load
CAT32HPD1BC2	50 mm	16 mm Max	165.1 mm	130.2 mm	440N
CAT48HPD1BC2	75 mm	16 mm Max	215.9 mm	171.5 mm	440N
CAT64HPD1BC2	100 mm	16 mm Max	266.7 mm	196.9 mm	440N


ADDITIONAL PRODUCT DETAILS

Static load limit of each J-Hook is 60 lb (270 N).

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

