

nVent CADDY Pyramid Tool-Free Cable Tray Support Kit



FEATURES

Push-in pins install without the need for additional tools

Plastic pins and base will not corrode

Pins and mounting holes accommodate most perforated cable tray

Ready to use out of the box, saving installation time and labor

Additional pins can be purchased separately

Foam bottom offers low abrasion interface for better roof membrane protection

Provides superior load distribution, even with varying rooftop surfaces

Compatible with roof surfaces including single ply, bituminous, metal and spray foam

Multiple sizes and load ratings offer the ability to tailor the solution to the application

Easy to transport to the roof

SPECIFICATIONS

Static Load Safety Factor: 3:1

Material: Polyethylene; Polypropylene; Nylon


Temperature: -45 to 65 °C

Table 1/1

Catalog Number	Length (L)	Width (W)	Height (H)	Surface Area	Unit Weight	Static Load
PTF6P	196mm	150 mm	102 mm	26452mm ²	0.3 kg	1330N

CatalogNumber	Length (L)	Width (W)	Height (H)	Surface Area	Unit Weight	Static Load
PTF10P	318mm	201 mm	102 mm	59355mm ²	0.5 kg	4450N
PTF16P	480mm	201 mm	102 mm	91613mm ²	1 kg	6670N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

