

# nVent CADDY Speed Link SLK with Angle Bracket



## CERTIFICATIONS



## FEATURES

Complete system includes wire, locking device and pre-assembled angle bracket end fitting

Ideal for attaching to concrete, steel or wood surfaces

Simple alternative to jack chain and additional hardware

## SPECIFICATIONS

|                                   |                                |
|-----------------------------------|--------------------------------|
| <b>Static Load Safety Factor:</b> | 5:1                            |
| <b>Finish:</b>                    | Electrogalvanized              |
| <b>Material:</b>                  | Steel;Zinc Alloy;Polypropylene |
| <b>Complies With:</b>             | SMACNA HVAC-DCS                |

Table 1/2

| Catalog Number | Wire Rope Diameter | Wire Rope Length | A       | Hole Size (HS) | Height (H) | Width (W) |
|----------------|--------------------|------------------|---------|----------------|------------|-----------|
| SLK15L1AB      | 1.5 mm             | 1m               | 22.6 mm | 7.1 mm         | 55 mm      | 19 mm     |


| CatalogNumber | Wire Rope Diameter | Wire Rope Length | A       | Hole Size (HS) | Height (H) | Width (W) |
|---------------|--------------------|------------------|---------|----------------|------------|-----------|
| SLK15L2AB     | 1.5 mm             | 2m               | 22.6 mm | 7.1 mm         | 55 mm      | 19 mm     |
| SLK15L3AB     | 1.5 mm             | 3m               | 22.6 mm | 7.1 mm         | 55 mm      | 19 mm     |
| SLK15L5AB     | 1.5 mm             | 5m               | 22.6 mm | 7.1 mm         | 55 mm      | 19 mm     |
| SLK2L2AB      | 2 mm               | 2m               | 22.6 mm | 7.1 mm         | 55 mm      | 19 mm     |
| SLK2L3AB      | 2 mm               | 3m               | 22.6 mm | 7.1 mm         | 55 mm      | 19 mm     |
| SLK2L5AB      | 2 mm               | 5m               | 22.6 mm | 7.1 mm         | 55 mm      | 19 mm     |
| SLK3L10AB     | 3 mm               | 10m              | 22.6 mm | 7.1 mm         | 62 mm      | 24 mm     |
| SLK3L5AB      | 3 mm               | 5m               | 22.6 mm | 7.1 mm         | 62 mm      | 24 mm     |
| SLK3L7AB      | 3 mm               | 7m               | 22.6 mm | 7.1 mm         | 62 mm      | 24 mm     |

Table 2/2

| Catalog Number | Thickness (T) | Angle (a) | Static Load | Certifications |
|----------------|---------------|-----------|-------------|----------------|
| SLK15L1AB      | 12.5 mm       | 90 ° Max  | 195N        | ITB, UL, cUL   |
| SLK15L2AB      | 12.5 mm       | 90 ° Max  | 195N        | ITB, UL, cUL   |
| SLK15L3AB      | 12.5 mm       | 90 ° Max  | 195N        | cUL, ITB, UL   |
| SLK15L5AB      | 12.5 mm       | 90 ° Max  | 195N        | ITB, UL, cUL   |
| SLK2L2AB       | 12.5 mm       | 90 ° Max  | 440N        | ITB, UL, cUL   |
| SLK2L3AB       | 12.5 mm       | 90 ° Max  | 440N        | ITB, UL, cUL   |
| SLK2L5AB       | 12.5 mm       | 90 ° Max  | 440N        | ITB, UL, cUL   |
| SLK3L10AB      | 16 mm         | 90 ° Max  | 890N        |                |

| Catalog Number | Thickness (T) | Angle (a) | Static Load | Certifications |
|----------------|---------------|-----------|-------------|----------------|
| SLK3L5AB       | 16 mm         | 90 ° Max  | 890N        |                |
| SLK3L7AB       | 16 mm         | 90 ° Max  | 890N        |                |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
 Option 1 – Customer Care  
 Option 2 – Technical Support

#### Europe

Netherlands:  
 +31 800-0200135  
 France:  
 +33 800 901 793

#### Europe

Germany:  
 800 1890272  
 Other Countries:  
 +31 13 5835404

#### APAC

Shanghai:  
 + 86 21 2412 1618/19  
 Sydney:  
 +61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

