

nVent CADDY Speed Link SLK with Hook



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

Also available in Y-hook configuration

SPECIFICATIONS

Static Load Safety Factor:	5:1
Finish:	Electrogalvanized
Material:	Steel; Polypropylene; Zinc Alloy
Complies With:	SMACNA HVAC-DCS

Table 1/2

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	C	Height (H)
----------------	--------------------	------------------	---	---	---	------------


SLK15L1	1.5 mm	1m	48 mm	18 mm	4.5 mm	55 mm
SLK15L10	1.5 mm	10m	48 mm	18 mm	4.5 mm	55 mm
SLK15L2	1.5 mm	2m	48 mm	18 mm	4.5 mm	55 mm
SLK15L2R2	1.5 mm	2m	48 mm	18 mm	4.5 mm	55 mm
SLK15L3	1.5 mm	3m	48 mm	18 mm	4.5 mm	55 mm
SLK15L3R2	1.5 mm	3m	48 mm	18 mm	4.5 mm	55 mm
SLK15L5	1.5 mm	5m	48 mm	18 mm	4.5 mm	55 mm
SLK15L5R2	1.5 mm	5m	48 mm	18 mm	4.5 mm	55 mm
SLK2L1	2 mm	1m	57 mm	22 mm	5.5 mm	55 mm
SLK2L10	2 mm	10m	57 mm	22 mm	5.5 mm	55 mm
SLK2L2	2 mm	2m	57 mm	22 mm	5.5 mm	55 mm
SLK2L2R2	2 mm	2m	57 mm	22 mm	5.5 mm	55 mm
SLK2L3	2 mm	3m	57 mm	22 mm	5.5 mm	55 mm
SLK2L3R2	2 mm	3m	57 mm	22 mm	5.5 mm	55 mm
SLK2L5	2 mm	5m	57 mm	22 mm	5.5 mm	55 mm
SLK3L1	3 mm	1m	57.6 mm	23.2 mm	6.1 mm	62 mm
SLK3L10	3 mm	10m	57.6 mm	23.2 mm	6.1 mm	62 mm
SLK3L2	3 mm	2m	57.6 mm	23.2 mm	6.1 mm	62 mm
SLK3L3	3 mm	3m	57.6 mm	23.2 mm	6.1 mm	62 mm

SLK3L3R2	3 mm	3m	57.6 mm	23.2 mm	6.1 mm	62 mm
SLK3L5	3 mm	5m	57.6 mm	23.2 mm	6.1 mm	62 mm
SLK3L5R2	3 mm	5m	57.6 mm	23.2 mm	6.1 mm	62 mm

Table 2/2					
Catalog Number	Width (W)	Thickness (T)	Angle (a)	Static Load	Certifications
SLK15L1	19 mm	12.5 mm	90 ° Max	195N	UL, cUL, SMACNA
SLK15L10	19 mm	12.5 mm	90 ° Max	195N	SMACNA, UL, cUL
SLK15L2	19 mm	12.5 mm	90 ° Max	195N	SMACNA, UL, cUL
SLK15L2R2	19 mm	12.5 mm	90 ° Max	195N	SMACNA, UL, cUL
SLK15L3	19 mm	12.5 mm	90 ° Max	195N	UL, cUL, SMACNA
SLK15L3R2	19 mm	12.5 mm	90 ° Max	195N	UL, cUL, SMACNA
SLK15L5	19 mm	12.5 mm	90 ° Max	195N	SMACNA, UL, cUL
SLK15L5R2	19 mm	12.5 mm	90 ° Max	195N	UL, cUL, SMACNA
SLK2L1	19 mm	12.5 mm	90 ° Max	440N	SMACNA, UL, cUL
SLK2L10	19 mm	12.5 mm	90 ° Max	440N	SMACNA, UL, cUL
SLK2L2	19 mm	12.5 mm	90 ° Max	440N	UL, cUL, SMACNA
SLK2L2R2	19 mm	12.5 mm	90 ° Max	440N	UL, cUL, SMACNA
SLK2L3	19 mm	12.5 mm	90 ° Max	440N	SMACNA, UL, cUL
SLK2L3R2	19 mm	12.5 mm	90 ° Max	440N	SMACNA, UL, cUL
SLK2L5	19 mm	12.5 mm	90 ° Max	440N	UL, cUL, SMACNA

Catalog Number	Width (W)	Thickness (T)	Angle (a)	Static Load	Certifications
SLK3L1	24 mm	16 mm	90 ° Max	890N	SMACNA
SLK3L10	24 mm	16 mm	90 ° Max	890N	SMACNA
SLK3L2	24 mm	16 mm	90 ° Max	890N	SMACNA
SLK3L3	24 mm	16 mm	90 ° Max	890N	SMACNA
SLK3L3R2	24 mm	16 mm	90 ° Max	890N	SMACNA
SLK3L5	24 mm	16 mm	90 ° Max	890N	SMACNA
SLK3L5R2	24 mm	16 mm	90 ° Max	890N	SMACNA

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

