

nVent CADDY Swift Clip Threaded Rod Attachment



FEATURES

- Snap-on and twist installation requires no tools
- Easily adjusts by rotating up or down on the threaded rod
- For support and positioning of refrigeration, A/C tubing, PEX piping, conduit and cabling
- Secures pipe and insulation without any breaks
- Compliant with UL® 2043 and suitable for use in air handling (plenum) spaces

SPECIFICATIONS

- Material:** Polyamide
- Working Temperature:** -40 to 140 °C

Table 1/1

Catalog Number	Outer Diameter	Copper Tube Size
TRC212	54 mm	2"
TRC162	41.3 mm	1 1/2"
TRC125	31.75 mm	
TRC137	34.9 mm	1 1/4"

Catalog Number	Outer Diameter	Copper Tube Size
TRC112	28.6 mm	1"
TRC100	25.4 mm	
TRC200	50.8 mm	
TRC087	22.2 mm	3/4"
TRC150	38.1 mm	
TRC075	19.1 mm	5/8"
TRC062	15.9 mm	1/2"

ADDITIONAL PRODUCT DETAILS

Clip must be installed with temperature at or above 14 °F (-10 °C).

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

