

PAR Parallel Pipe and Conduit Clamp



FEATURES

Fix pipe or conduit parallel to a beam

SPECIFICATIONS

Material: Cast Iron

Finish: Hot-Dip Galvanized

Table 1/1

Catalog Number	Flange Thickness
PAR0050HD	19.1 mm Max
PAR0075HD	19.1 mm Max
PAR0100HD	19.1 mm Max
PAR0150HD	19.1 mm Max
PAR0200HD	19.1 mm Max
PAR0125HD	19.1 mm Max

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

