


# Threaded Rod



## FEATURES

Cut to length as needed

According to standard DIN 976-1 / ISO 7412

Property Class 4.8

## SPECIFICATIONS


<b>Tensile Strength:</b>	400 MPa
<b>Yield Strength:</b>	248211kPa
<b>Finish:</b>	Electrogalvanized
<b>Material:</b>	Steel

Table 1/1

Catalog Number	Rod Size (RS)	Length (L)	Static Load
0502506EG	1/4"	1800mm	1068N
0502510EG	1/4"	3000mm	1068N
0503706EG	3/8"	1800mm	2700N
0503710EG	3/8"	3000mm	2712N
0505006EG	1/2"	1800mm	5026N

Catalog Number	Rod Size (RS)	Length (L)	Static Load
0505010EG	1/2"	3000mm	5026N
0506206EG	5/8"	1800mm	8050N
0506210EG	5/8"	3000mm	8050N
0507506EG	3/4"	1800mm	12054N
0507510EG	3/4"	3050mm	12054N
0508706EG	7/8"	1800mm	16770N
0508710EG	7/8"	3050mm	16770N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**

