

WBT Performance Cable Tray Ceiling Support



In the evolving landscape of cable management, the nVent CADDY WBT Performance Tray Ceiling Support is a simple and efficient alternative to traditional strut trapeze systems for wire basket tray installations. Engineered for simplicity and strength, this support solution not only anchors wire basket trays securely to the ceiling but also doubles as a splice point—making it a dual-function component that enhances both structural integrity and installation efficiency.

Compatible with varying nVent CADDY WBT Performance Cable Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its prepunched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a center support or support provisioned from both ends

Designed to be used with the nVent CADDY WBT Performance Cable Tray Ground Splice and nVent CADDY WBT Performance Cable Tray Splice Kit

Supported with 3/8 or ½ in threaded rod

SPECIFICATIONS

Material: Steel

Table 1/2						
Catalog Number	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)
WBTCLSPRT6	Pregalvanized		15.75 mm	41.4 mm	238.404mm	13.49 mm
WBTCLSPRT6B A	Pregalvanized	Black	15.75 mm	41.4 mm	238.404mm	13.49 mm


CatalogNumber	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)
WBTCLSPRT6W H	Pregalvanized	White	15.75 mm	41.4 mm	238.404mm	13.49 mm
WBTCLSPRT8	Pregalvanized		15.75 mm	41.4 mm	288.392mm	13.49 mm
WBTCLSPRT8B A	Pregalvanized	Black	15.75 mm	41.4 mm	288.392mm	13.49 mm
WBTCLSPRT8W H	Pregalvanized	White	15.75 mm	41.4 mm	288.392mm	13.49 mm
WBTCLSPRT12	Electrogalvaniz ed		15.75 mm	41.4 mm	388.417mm	13.49 mm
WBTCLSPRT12 BA	Electrogalvaniz ed	Black	15.75 mm	41.4 mm	388.417mm	13.49 mm
WBTCLSPRT12 WH	Electrogalvaniz ed	White	15.75 mm	41.4 mm	388.417mm	13.49 mm
WBTCLSPRT16	Pregalvanized		15.75 mm	41.4 mm	488.417mm	13.49 mm
WBTCLSPRT16 BA	Pregalvanized	Black	15.75 mm	41.4 mm	488.417mm	13.49 mm
WBTCLSPRT16 WH	Pregalvanized	White	15.75 mm	41.4 mm	488.417mm	13.49 mm
WBTCLSPRT18	Electrogalvaniz ed		15.75 mm	41.4 mm	538.226mm	13.49 mm
WBTCLSPRT18 BA	Electrogalvaniz ed	Black	15.75 mm	41.4 mm	538.226mm	13.49 mm
WBTCLSPRT18 WH	Electrogalvaniz ed	White	15.75 mm	41.4 mm	538.226mm	13.49 mm
WBTCLSPRT20	Pregalvanized		15.75 mm	41.4 mm	588.442mm	13.49 mm
WBTCLSPRT20 BA	Pregalvanized	Black	15.75 mm	41.4 mm	588.442mm	13.49 mm

CatalogNumber	Finish	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)
WBTCLSPRT20 WH	Pregalvanized	White	15.75 mm	41.4 mm	588.442mm	13.49 mm
WBTCLSPRT24	Electrogalvaniz ed		15.75 mm	41.4 mm	688.442mm	13.49 mm
WBTCLSPRT24 BA	Electrogalvaniz ed	Black	15.75 mm	41.4 mm	688.442mm	13.49 mm
WBTCLSPRT24 WH	Electrogalvaniz ed	White	15.75 mm	41.4 mm	688.442mm	13.49 mm

Table 2/2				
Catalog Number	Unit Weight			
WBTCLSPRT6	0.249 kg			
WBTCLSPRT6BA	0.249 kg			
WBTCLSPRT6WH	0.249 kg			
WBTCLSPRT8	0.363 kg			
WBTCLSPRT8BA	0.363 kg			
WBTCLSPRT8WH	0.363 kg			
WBTCLSPRT12	0.499 kg			
WBTCLSPRT12BA	0.499 kg			
WBTCLSPRT12WH	0.499 kg			
WBTCLSPRT16	0.68 kg			
WBTCLSPRT16BA	0.68 kg			
WBTCLSPRT16WH	0.68 kg			

Catalog Number	Unit Weight
WBTCLSPRT18	0.726 kg
WBTCLSPRT18BA	0.726 kg
WBTCLSPRT18WH	0.726 kg
WBTCLSPRT20	0.862 kg
WBTCLSPRT20BA	0.862 kg
WBTCLSPRT20WH	0.862 kg
WBTCLSPRT24	0.862 kg
WBTCLSPRT24BA	0.862 kg
WBTCLSPRT24WH	0.862 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

