

WBT Performance Cable Tray Center Support



The nVent CADDY WBT Performance Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY WBT Performance Cable Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY WBT Performance Cable Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Color	Height	Width	Length	Height 1	Height 2
WBTCTSPRT12		193.55 mm	41.4 mm	292.176mm	15.75mm	177.8mm
WBTCTSPRT12 WH	White	193.55 mm	41.4 mm	292.176mm	15.75mm	177.8mm
WBTCTSPRT4		193.55 mm	41.4 mm	105.156mm	15.75mm	177.8mm

CatalogNumber	Color	Height	Width	Length	Height 1	Height 2
WBTCTSPRT4B A	Black	193.55 mm	41.4 mm	105.156mm	15.75mm	177.8mm
WBTCTSPRT4 WH	White	193.55 mm	41.4 mm	105.156mm	15.75mm	177.8mm
WBTCTSPRT6		193.55 mm	41.4 mm	147.777mm	15.75mm	177.8mm
WBTCTSPRT6 WH	White	193.55 mm	41.4 mm	147.777mm	15.75mm	177.8mm
WBTCTSPRT8		193.55 mm	41.4 mm	190.551mm	15.75mm	177.8mm
WBTCTSPRT8 WH	White	193.55 mm	41.4 mm	190.551mm	15.75mm	177.8mm

Table 2/2

Catalog Number	Hole Size 1	Hole Size 2	Unit Weight
WBTCTSPRT12	7.137 mm	5.79 mm	1.225 kg
WBTCTSPRT12WH	7.137 mm	5.79 mm	1.225 kg
WBTCTSPRT4	7.137 mm	5.79 mm	0.7 kg
WBTCTSPRT4BA	7.137 mm	5.79 mm	0.7 kg
WBTCTSPRT4WH	7.137 mm	5.79 mm	0.7 kg
WBTCTSPRT6	7.137 mm	5.79 mm	0.816 kg
WBTCTSPRT6WH	7.137 mm	5.79 mm	0.816 kg
WBTCTSPRT8	7.137 mm	5.79 mm	0.907 kg
WBTCTSPRT8WH	7.137 mm	5.79 mm	0.907 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

