

Cable Spool, Stainless Steel

Data Solutions



FEATURES

Cut to length as needed

Pre-stretched restraint cable

Certified chemically compatible with CPVC piping systems

SPECIFICATIONS

Static Load Safety Factor: 1.5:1

Material: Stainless Steel 316 (EN 1.4401)

Table 1/1

Catalog Number	Brace Size	Diameter	Cable Length	Static Load
CSB12CBLSS	#12	2.4mm	76.2m	1410N
CSB18CBLSS	#18	3.2mm	76.2m	2750N
CSB36CBLSS	#36	4.8mm	76.2m	5860N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE