

nVent CADDY Cat HP Double J-Hook with Hammer-On Flange Clip, Swivel

Data Solutions



FEATURES

Low-profile configuration providing double J-Hook capacity

Requires only a hammer to install

Rotates 360 degrees to support various directional runs of cable

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

SPECIFICATIONS

Finish: Pregalvanized; nVent CADDY Armour

Material: Steel; Spring Steel

Table 1/1

Catalog Number	Diameter (Ø)	Flange Thickness (FT)	Width (W)	A	Static Load
----------------	--------------	-----------------------	-----------	---	-------------


CAT32HPD1M24	50mm	3 – 6mm	165.1mm	130.2mm	440N
CAT48HPD1M24	75mm	3 – 6mm	215.9mm	171.5mm	440N

ADDITIONAL PRODUCT DETAILS

Static load limit of each J-Hook is 60 lb (270 N).

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE