


nVent CADDY Cat HP J-Hook with Hammer-On Flange Clip

Data Solutions



CERTIFICATIONS



FEATURES

Requires only a hammer to install

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

SPECIFICATIONS

Finish: Pregalvanized; nVent CADDY Armour

Material: Steel; Spring Steel

Table 1/2

Catalog Number	Diameter (Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Flange Thickness (FT)
CAT16HP24SM	25mm	690mm ²	20	15	10	3 – 8mm
CAT21HP24SM	33.3mm	1174mm ²	50	40	25	3 – 8mm
CAT32HP24SM	50mm	2561mm ²	90	60	35	3 – 8mm
CAT48HP24SM	75mm	5974mm ²	200	150	80	3 – 8mm
CAT64HP24SM	100mm	9987mm ²	330	220	140	3 – 8mm
CAT16HP58SM	25mm	690mm ²	20	15	10	8 – 14mm
CAT21HP58SM	33.3mm	1174mm ²	50	40	25	8 – 14mm
CAT32HP58SM	50mm	2561mm ²	90	60	35	8 – 14mm
CAT48HP58SM	75mm	5974mm ²	200	150	80	8 – 14mm
CAT64HP58SM	100mm	9987mm ²	330	220	140	8 – 14mm
CAT16HP912SM	25mm	690mm ²	20	15	10	14 – 20mm
CAT21HP912SM	33.3mm	1174mm ²	50	40	25	14 – 20mm
CAT32HP912SM	50mm	2561mm ²	90	60	35	14 – 20mm
CAT48HP912SM	75mm	5974mm ²	200	150	80	14 – 20mm
CAT64HP912SM	100mm	9987mm ²	330	220	140	14 – 20mm

Table 2/2

Catalog Number	Static Load
----------------	-------------


CAT16HP24SM	270N
CAT21HP24SM	270N
CAT32HP24SM	270N
CAT48HP24SM	270N
CAT64HP24SM	270N
CAT16HP58SM	270N
CAT21HP58SM	270N
CAT32HP58SM	270N
CAT48HP58SM	270N
CAT64HP58SM	270N
CAT16HP912SM	270N
CAT21HP912SM	270N
CAT32HP912SM	270N
CAT48HP912SM	270N
CAT64HP912SM	270N

ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE