

Open Frame Rack-Mount Steel Shelf

Data Solutions



The Open-Frame Rack-Mount Steel Shelf mounts to the front of the rack and is ideal for holding non-19-in. rack-mount equipment. It is available with or without vents. Please note the load rating is 100 lb. (45.4 kg).

FEATURES

The Open-Frame Rack-Mount Steel Shelf mounts to the front of the rack and is ideal for holding non-19-in. rack-mount equipment

It is available with or without vents. Please note the load rating is 100 lb. (45.4 kg)

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Color	Color Code	Thickness
EMSV1922	13268	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
EMS1922	13267	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
EMSV1918	13271	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm
EMS1918	13266	Mild Steel	Powder Coated	Jet Black	RAL 9005	1.52mm

Table 2/2

Catalog Number	Article Number	Height	Width	Depth	Rack Units	Type
----------------	----------------	--------	-------	-------	------------	------

EMSV1922	13268	133mm	482mm	559mm	3U	Vented
EMS1922	13267	133mm	482mm	559mm	3U	Solid
EMSV1918	13271	133mm	482mm	457mm	3U	Vented
EMS1918	13266	133mm	482mm	457mm	3U	Solid

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE