

ProLine Pagoda Exhaust Vents

Data Solutions

Pagoda Exhaust Vents can be field-installed on any ProLine or ProLine G2 solid top to provide active enclosure cooling.



FEATURES

Axial fan and finger guard mounted in housing

Drip-protected, raised cover is removable from the inside of the enclosure

115V or 230V versions with lead wires

115V power cord option

Rated UL Type 1; installing this component on an enclosure brings the enclosure rating to UL Type 1

Includes gasket and mounting hardware

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Voltage AC	Color	Color Code	Finish
PPT1C	11095	Mild Steel	115V	Light Gray	RAL 7035	Powder Coated

Table 2/2

Catalog Number	Article Number	Thickness
PPT1C	11095	1.9mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE