

Plug Bond, Signal, Copper, Steel, Carbon Steel, EG, Tinned, PG, 0.334" Diameter, 46"

CATALOG NUMBER

SBPAJB46



FEATURES

Designed for application to the rail web

Hammered into a 3/8" (9.5 mm) diameter hole drilled through the rail web and driven from the same side the hole was drilled

Recommended method of installation requires a bond 12" (304.8 mm) longer than the splice bar

PRODUCT ATTRIBUTES

Material: Copper;Steel;Carbon Steel

Finish: Electrogalvanized;Tinned;Pregalvanized

Conductor Size: 0.334" Diameter

Length (L): 1168.4mm

Diameter 1 (Ø1): 8.5 mm


Diameter 2 (Ø2): 10.5 mm

Depth (D): 31 3/4mm

ADDITIONAL PRODUCT DETAILS

Plug Bond Grease (T369) recommended when installing.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE